Product data sheet

Specifications





Wall rack VDM 7U swi chass D400

NSYVDM7U4P

- Discontinued on: May 19, 2023
- ! End-of-service on: Jul 6, 2023

① Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	Spacial
Product Name	Spacial VDM
Application	Electronic application
Product Or Component Type	Compact enclosure
Body Type	1-body
Rack Type	Swing
Enclosure Nominal Height	15.75 in (400 mm)
Enclosure Nominal Width	23.62 in (600 mm)
Enclosure Nominal Depth	15.75 in (400 mm)
Installation Accessory Type	Wall-mounting
Product Destination	Electronics and networks
Device Composition	1 cable gland plate bottom 2 lock 19" swing rack 1 body 1 door with lock 1 19" swing rack

Complementary

Door Type	Glass
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	3 mm double-bar lock
Type Of Gland Plate	Standard
Number Of Units 19"	7
Accessibility For Operation	Front
Removable Parts	Door by hinges Rack by fixing element
Material	Enclosure and 19" rack steel
Surface Finish	Enclosure and 19" rack epoxy-polyester powder
Color	Enclosure and 19" rack Gray RAL 7035)
Standards	IEC 62208
Net Weight	41.40 lb(US) (18.78 kg)
Width	23.62 in (600 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Height	15.75 in (400 mm)
Depth	15.75 in (400 mm)

Environment

Ip Degree Of Protection	IP66 IEC 60529	
Ik Degree Of Protection	IK08 IEC 62262	

Ordering and shipping details

_	· · · · ·
Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480174513
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24.80 in (63.0 cm)
Package 1 Width	16.54 in (42.0 cm)
Package 1 Length	16.54 in (42.0 cm)
Package 1 Weight	41.40 lb(US) (18.78 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile