





Load center accessory, QO/ Homeline, ground bar kit, 23 terminals, with AWG 1-4/0 lug in aluminum or copper

PK23GTAL

Product availability: Stock - Normally stocked in distribution facility

Price\*: 40.70 USD

#### Main

Product Line	QO
Product Type	Bar

## Complementary

Number Of Connectors	24	
Wire Size	AWG 14AWG 4 copper AWG 12AWG 4 aluminium AWG 4AWG 1 aluminium/copper	
Provided Equipment	2 screw	
Bar Length	9.45 in (240 mm)	
Maximum Length Of Segment	3.15 in (80 mm)	
Device Mounting	Direct mounting back of enclosure	
Height	0.437 in (11.10 mm)	
Depth	0.312 in (7.92 mm)	
Tightening Torque	30 lb.in  Mounting screw 30 lb.in 20 lb.in, AWG 14AWG 10, copper 20 lb.in, AWG 12AWG 10, aluminium 35 lb.in, AWG 6AWG 4 25 lb.in, AWG 8 25 lb.in, AWG 14AWG 12, copper 25 lb.in, AWG 12AWG 10, aluminium	

### Ordering and shipping details

_		
Category	US1DE3A00102	
Discount Schedule	DE3A	
Gtin	785901440895	
Returnability Yes		
Country Of Origin	LIC	

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.20 in (0.762 am)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	1.60 in (4.064 cm)	
Package 1 Length	8.10 in (20.574 cm)	
Package 1 Weight	6.40 oz (181.437 g)	
Unit Type Of Package 2	PAL	
Number Of Units In Package 2	1100	
Package 2 Height	40.00 in (101.6 cm)	
Package 2 Width	40.00 in (101.6 cm)	
Package 2 Length	48.00 in (121.92 cm)	
Package 2 Weight	469.42 lb(US) (212.926 kg)	

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov