

# Product data sheet

Specifications

SQUARE D

Green Premium™



## Busway I-Line Circuit Breaker Plug-in Unit, 30A, FA Frame, 480V, 4 Wire

PFA34030GN

⚠ Discontinued on: Nov 20, 2023

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1,978.00 USD

### Main

Product Or Component Type	Plug-in unit
Range Of Product	I-Line
Circuit Breaker Type	FA
Trip Unit Technology	Thermal-magnetic

### Complementary

Protection Type	Circuit breaker
Mounting Mode	Plug-in
[Ue] Rated Operational Voltage	277/480 V AC
Line Rated Current	30 A
Number Of Phases	3 phase
Poles Description	3P
Interrupt Rating	25 kA 240 V AC 18 kA 480 V AC
Wiring Configuration	4-wire (integral ground bus)
Awg Gauge	AWG 14...AWG 4 1 phase and neutral AWG 10...AWG 2 1 ground
Depth	8.62 in (219 mm)
Height	8.27 in (210 mm)
Width	14.37 in (365 mm)

### Environment

Product Certifications	CSA C22.2 No 27 UL listed file E22182
Standards	UL 857

### Ordering and shipping details

Category	20182 - PFA / PHD C/B PLUGS
Discount Schedule	PE7
Gtin	785901022206

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

<b>Returnability</b>	No
----------------------	----

---

<b>Country Of Origin</b>	US
--------------------------	----

## Packing Units

---

<b>Unit Type Of Package 1</b>	PCE
-------------------------------	-----

---

<b>Number Of Units In Package 1</b>	1
-------------------------------------	---

---

<b>Package 1 Height</b>	10.00 in (25.4 cm)
-------------------------	--------------------

---

<b>Package 1 Width</b>	11.00 in (27.94 cm)
------------------------	---------------------

---

<b>Package 1 Length</b>	15.50 in (39.37 cm)
-------------------------	---------------------

---

<b>Package 1 Weight</b>	18.50 lb(US) (8.392 kg)
-------------------------	-------------------------

## Contractual warranty

---

<b>Warranty</b>	18 months
-----------------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

 Mercury Free

 RoHS Exemption Information Yes

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu RoHS Directive Compliant with Exemptions

China RoHS Regulation [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information.

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile No need of specific recycling operations

California Proposition 65 WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)