

# Product data sheet

Specifications



Plug-in unit, I-Line Busway, F-frame, 40A, 3 phase, 3 wire, 480VAC, 25kA, ground

PFA34040G

Product availability: Non-Stock - Not normally stocked in distribution facility

⚠ Discontinued

Price\*: 1,776.00 USD

## Main

|                           |              |
|---------------------------|--------------|
| Range Of Product          | I-Line       |
| Product Or Component Type | Plug-in unit |
| Module Type               | F-Frame      |

## Complementary

|                                |                                       |
|--------------------------------|---------------------------------------|
| [Ue] Rated Operational Voltage | 480 V AC                              |
| Phase                          | 3 phase                               |
| [Ie] Rated Operational Current | 40 A                                  |
| Number Of Poles                | 3                                     |
| Busbar Description             | Ground                                |
| Breaking Capacity Code         | A                                     |
| Disconnecter Device Type       | Thermal magnetic circuit breaker 40 A |
| Wiring Configuration           | 3-wire                                |

## Environment

|                        |           |
|------------------------|-----------|
| Product Certifications | UL<br>CSA |
|------------------------|-----------|

## Ordering and shipping details

|                   |                             |
|-------------------|-----------------------------|
| Category          | 20182 - PFA / PHD C/B PLUGS |
| Discount Schedule | PE7                         |
| Gtin              | 00785901018568              |
| Returnability     | No                          |
| Country Of Origin | US                          |

## Packing Units

|                              |     |
|------------------------------|-----|
| Unit Type Of Package 1       | PCE |
| Number Of Units In Package 1 | 1   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Mercury Free

 RoHS Exemption Information   [Yes](#)

## Certifications & Standards

|                           |                                                                                                                                                                                                                                                                                                                                                             |
|---------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Reach Regulation          | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                                           |
| Eu Rohs Directive         | Compliant with Exemptions                                                                                                                                                                                                                                                                                                                                   |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information.                                                                                                                                                                                                                                      |
| Environmental Disclosure  | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                               |
| Circularity Profile       | No need of specific recycling operations                                                                                                                                                                                                                                                                                                                    |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |