





# Circuit breaker, PowerPacT Q, 200A, 2 pole, 240VAC, 65kA, I-Line, thermal magnetic, 80%, AB

QGA222001

Product availability: Stock - Normally stocked in distribution facility

Price\*: 1,593.00 USD

### Main

Range	PowerPact
Product Name	PowerPact Q
Product Or Component Type	Circuit breaker
Device Application	Distribution

## Complementary

200 A	
2P	
Operating handle	
G	
65 kA 120/208 V AC 50/60 Hz UL 65 kA 240 V AC 50/60 Hz UL	
240 V AC 50/60 Hz UL	
50/60 Hz	
Rated Impulse Withstand 8 kV UL e	
Thermal-magnetic	
2400 A	
1200 A	
80 %	
Category A	
1000 cycles loaded 5000 cycles no load	
1 trip indicator green)	
I-Line bracket)	
Bracket	
I-Line connection, line Lugs, load	
3 in (76.20 mm)	
<b>Torque</b> 247.82 lbf.in (28 N.m) 0.040.23 in² (25150 mm²) (AWG 4300 kcmil)	
0.87 in (22 mm)	
Height 6.47 in (164.34 mm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	3 in (76.20 mm)	
Depth	3.93 in (99.82 mm)	
Phase Connection	AB	
Circuit Breaker Application	HACR rated	

## **Environment**

Standards	UL CSA NEMA NOM-003-SCFI-2000
Product Certifications	UL CSA NOM
Ambient Air Temperature For Operation	104158 °F (4070 °C)

# Ordering and shipping details

Category	US10DE201023	
Discount Schedule	0DE2	
Gtin	785901438922	
Returnability	Yes	
Country Of Origin	MX	

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	4.60 in (11.684 cm)	
Package 1 Width	7.70 in (19.558 cm)	
Package 1 Length	12.50 in (31.75 cm)	
Package 1 Weight	4.75 lb(US) (2.155 kg)	

## **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Mercury Free	
<b>Ø</b>	Rohs Exemption Information	'es
<b>⊘</b>	Pvc Free	
<b>Ø</b>	Halogen Free Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov