





Load center accessory, QO/ Homeline, ground bar kit, 12 terminals

PK12GTA

Product availability: Stock - Normally stocked in distribution

Price*: 15.80 USD

Main

Product Line	QO
Product Type	Bar

Complementary

· · · · · · · · · · · · · · · · · ·		
Number Of Connectors	12	
Wire Size	AWG 14AWG 4 copper AWG 12AWG 4 aluminium	
Provided Equipment 2 screw		
Bar Length	4.69 in (119 mm)	
Maximum Length Of Segment 3.15 in (80 mm)		
Device Mounting Direct mounting back of enclosure		
Height	0.437 in (11.10 mm) 0.437 in (11.10 mm)	
Depth	0.312 in (7.92 mm) 0.312 in (7.92 mm)	
Tightening Torque	30 lb.in Mounting screw 30 lb.in 20 lb.in, AWG 14AWG 10, copper 20 lb.in, AWG 12AWG 10, aluminium 35 lb.in, AWG 6AWG 4 25 lb.in, AWG 8 25 lb.in, AWG 14AWG 12, copper 25 lb.in, AWG 12AWG 10, aluminium	

Ordering and shipping details

Category	US1DE3A00102
Discount Schedule	DE3A
Gtin	785901026402
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	0.70 in (1.78 cm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	1.20 in (3.05 cm)	
Package 1 Length	4.80 in (12.19 cm)	
Package 1 Weight	2.08 oz (58.97 g)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov