





Load center accessory, QO/ Homeline, ground bar kit, 21 terminals

PK15GTA6

Product availability: Stock - Normally stocked in distribution facility

Price*: 53.00 USD

Main

Product Line	QO
Product Type	Bar

Complementary

J	
Number Of Connectors	21
Wire Size	AWG 14AWG 4 copper
	AWG 12AWG 4 aluminium
	AWG 6AWG 3/0 aluminium/copper
Provided Equipment	2 screw
Bar Length	5.87 in (149 mm)
	5.87 in (149 mm)
Maximum Length Of Segment	3.15 in (80 mm)
	5.24 in (133 mm)
Device Mounting	Direct mounting back of enclosure
Height	0.437 in (11.10 mm)
Depth	0.312 in (7.92 mm)
Tightening Torque	30 lb.in
	20 lb.in, AWG 14AWG 10, copper
	20 lb.in, AWG 12AWG 10, aluminium
	35 lb.in, AWG 6AWG 4
	25 lb.in, AWG 8
	25 lb.in, AWG 14AWG 12, copper
	25 lb.in, AWG 12AWG 10, aluminium
	,

Ordering and shipping details

Category	US1DE3A00102
Discount Schedule	DE3A
Gtin	785901328162
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.80 in (2.032 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	2.00 in (5.08 cm)	
Package 1 Length	5.80 in (14.732 cm)	
Package 1 Weight	6.40 oz (181.437 g)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov