





Load center accessory, QO/ Homeline, ground bar kit, 18 terminals, with AWG 1-4/0 lug in aluminum or copper

PK18GTAL

Product availability: Stock - Normally stocked in distribution facility

Price*: 37.80 USD

Main

Product Line	QO
Product Type	Bar

Complementary

Number Of Connectors	19	
Wire Size	AWG 14AWG 4 copper	
	AWG 12AWG 4 aluminium	
	AWG 4AWG 1 aluminium/copper	
Provided Equipment	2 QO 1 screw	
Bar Length	8.82 in (224 mm)	
Maximum Length Of Segment	3.15 in (80 mm)	
Device Mounting	Mounting holes back of enclosure	
Height	0.437 in (11.10 mm)	
Depth	0.312 in (7.92 mm)	
Tightening Torque	30 lb.in	
	Mounting screw 30 lb.in	
	20 lb.in, AWG 14AWG 10, copper	
	20 lb.in, AWG 12AWG 10, aluminium	
	35 lb.in, AWG 6AWG 4	
	25 lb.in, AWG 8	
	25 lb.in, AWG 14AWG 12, copper	
	25 lb.in, AWG 12AWG 10, aluminium	

Ordering and shipping details

Category	US1DE3A00102	
Discount Schedule	DE3A	
Gtin	785901440888	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.00 in (2.54 cm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	4.00 in (10.16 cm)	
Package 1 Length	8.50 in (21.59 cm)	
Package 1 Weight	5.92 oz (167.829 g)	
Unit Type Of Package 2	PAL	
Number Of Units In Package 2	1000	
Package 2 Height	40.00 in (101.6 cm)	
Package 2 Width	40.00 in (101.6 cm)	
Package 2 Length	48.00 in (121.92 cm)	
Package 2 Weight	398.36 lb(US) (180.692 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov