





# Load center accessory, QO/ Homeline, ground bar kit, 5 terminals

PK5GTA

Product availability: Stock - Normally stocked in distribution facility

Price\*: 11.70 USD

#### Main

| Product Line | QO  |
|--------------|-----|
| Product Type | Bar |

# Complementary

| Number Of Connectors      | 5   |  |
|---------------------------|---|--|
| Wire Size                 | AWG 14AWG 4 copper<br>AWG 12AWG 4 aluminium   |  |
| Provided Equipment        | 2 screw   |  |
| Bar Length                | 2.24 in (57 mm)   |  |
| Maximum Length Of Segment | gment 1.26 in (32 mm)   |  |
| Device Mounting           | Direct mounting back of enclosure   |  |
| Height                    | 0.437 in (11.10 mm)   |  |
| Depth                     | 0.312 in (7.92 mm)  |  |
| Tightening Torque         | 30 lb.in Mounting screw 30 lb.in 20 lb.in, AWG 14AWG 10, copper 20 lb.in, AWG 12AWG 10, aluminium 35 lb.in, AWG 6AWG 4 25 lb.in, AWG 8 25 lb.in, AWG 14AWG 12, copper 25 lb.in, AWG 12AWG 10, aluminium |  |

# Ordering and shipping details

| Category          | US1DE3A00102 |  |
|-------------------|--------------|--|
| Discount Schedule | ile DE3A     |  |
| Gtin              | 785901263654 |  |
| Returnability     | Yes          |  |
| Country Of Origin | US           |  |

## **Packing Units**

| Unit Type Of Package 1       | PCE                |
|------------------------------|--------------------|
| Number Of Units In Package 1 | 1                  |
| Package 1 Height             | 0.40 in (1.016 cm) |
| Package 1 Width              | 0.60 in (1.524 cm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Package 1 Length             | 2.30 in (5.842 cm)        |  |
|------------------------------|---------------------------|--|
| Package 1 Weight             | 1.12 oz (31.752 g)        |  |
| Unit Type Of Package 2       | PAL                       |  |
| Number Of Units In Package 2 | 2160                      |  |
| Package 2 Height             | 40.00 in (101.6 cm)       |  |
| Package 2 Width              | 40.00 in (101.6 cm)       |  |
| Package 2 Length             | 48.00 in (121.92 cm)      |  |
| Package 2 Weight             | 184.17 lb(US) (83.536 kg) |  |
|                              |                           |  |

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

| <b>Ø</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>Ø</b> | Toxic Heavy Metal Free     |     |
| <b>⊘</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

### **Certifications & Standards**

| Reach Regulation          | REACh Declaration   |
|---------------------------|---|
| Eu Rohs Directive         | Compliant EU RoHS Declaration   |
| China Rohs Regulation     | China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure  | Product Environmental Profile   |
| Circularity Profile       | No need of specific recycling operations  |
| California Proposition 65 | WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov                            |