


Product data sheet

Specifications

SQUARE D



Load center interior, QO, 1 phase, 12 spaces, 24 circuits, 125A convertible main lugs, NEMA3R, gnd bar, UL

QO11224L125GRBI

! Discontinued

! Discontinued on: Mar 11, 2022

Main

| | |
|--|--------------------------|
| Product Type | Load Center Interior |
| Marketing Trade Name | QO |
| Load Center Type | Convertible Mains (lugs) |
| Rated Current | 125 A |
| Number Of Spaces | 12 |
| Max Short Circuit Current Rating | 65 kA |
| Maximum Number Of Single Pole Circuits | 24 |
| Maximum Number Of Tandem Breakers | 12 |
| Number Of Phases | 1 phase |
| Voltage Rating | 120/240 V AC |

Complementary

| | |
|------------------------|--|
| Ground Bar | Grounding bar included (not installed) |
| Busbar Material | Tin plated copper: busbar |
| Product Certifications | UL Listed |
| Tightening Torque | 5.6 N.m, AWG 6...AWG 2/0 |

Environment

| | |
|---------------------------------------|---------------------------------|
| Ambient Air Temperature For Operation | 23 °F (-5 °C) 104 °F (40 °C) |
|---------------------------------------|---------------------------------|

Ordering and shipping details

| | |
|-------------------|-------------------------------|
| Category | 00199-DE5 MISC. SERVICE PARTS |
| Discount Schedule | DE5 |
| Returnability | No |

Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Weight | 10.00 lb(US) (4.536 kg) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | | |
|---|---|---|
|  | Reach Free Of Svhc | |
|  | Toxic Heavy Metal Free | |
|  | Mercury Free | |
|  | Rohs Exemption Information | Yes |
| Eu Rohs Directive | Compliant | EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration | Pro-active China RoHS declaration (out of China RoHS legal scope) |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov | |