

Product data sheet

Specifications



Mini circuit breaker, QO, 15A, 1 pole, 120/240VAC, 10kA, plug in, Powerlink

QO115PL

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 125.00 USD

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	15 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 240 V AC 10 kA 120 V AC
Number Of Panel Spaces	1
Provided Equipment	18 in (457.20 mm) lead
Wire Size	AWG 12...AWG 2 aluminium AWG 14...AWG 2 copper
Tightening Torque	35.40 lbf.in (4 N.m)
Height	4.57 in (116 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.50 lb(US) (0.227 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US1DE8A09650
----------	--------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Discount Schedule	DE8A
Gtin	785901095699
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.30 in (3.302 cm)
Package 1 Width	4.00 in (10.16 cm)
Package 1 Length	5.50 in (13.97 cm)
Package 1 Weight	8.00 oz (226.796 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

 Halogen Free Product

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information.

California Proposition 65 WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov