


Product data sheet

Specifications

SQUARE D



Load center interior, QO, 1 phase, 20 spaces, 20 circuits, 125A convertible main lugs, NEMA1, gnd bar, UL

QO120L125GI

! Discontinued

! Discontinued on: Jul 30, 2020

Main

Product Type	Load Center Interior
Marketing Trade Name	QO
Load Center Type	Convertible Mains (lugs)
Rated Current	125 A
Number Of Spaces	20
Max Short Circuit Current Rating	65 kA
Maximum Number Of Single Pole Circuits	20
Maximum Number Of Tandem Breakers	0
Number Of Phases	1 phase
Voltage Rating	120/240 V AC

Complementary

Ground Bar	Grounding bar included (not installed)
Busbar Material	Tin plated copper: busbar
Product Certifications	UL Listed
Tightening Torque	5.6 N.m, AWG 6...AWG 2/0

Environment

Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
---------------------------------------	---------------------------------

Ordering and shipping details

Category	00199-DE5 MISC. SERVICE PARTS
Discount Schedule	DE5
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.75 in (9.525 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	12.75 in (32.385 cm)
Package 1 Length	20.75 in (52.705 cm)
Package 1 Weight	10.00 lb(US) (4.536 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	