





Mini circuit breaker, QO, 20A, 1 pole, 120/240VAC, 10kA, plug in, Powerlink, load shedding

QO120PLILC

Product availability: Stock - Normally stocked in distribution facility

Price\*: 285.00 USD

#### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Ratings	Switching Duty rated
Electrical Connection	Box lugs

### Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 240 V AC 10 kA 120 V AC
Number Of Panel Spaces	1
Wire Size	AWG 12AWG 2 aluminium
Tightening Torque	35.40 lbf.in (4 N.m)
Height	4.57 in (116 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.47 lb(US) (0.213 kg)

#### **Environment**

Certifications	UL Listed CSA	
Ambient Rating	104 °F (40 °C)	

### Ordering and shipping details

Category	US1DE2A00026
Discount Schedule	DE2A
Gtin	785901446477
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.80 in (9.652 cm)
Package 1 Width	1.30 in (3.302 cm)
Package 1 Length	5.50 in (13.97 cm)
Package 1 Weight	7.36 oz (208.655 g)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

### Well-being performance

<b>Ø</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Product	

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations