

Product data sheet

Specifications

SQUARE D

Green Premium™



Mini circuit breaker, QO, 20A, 1 pole, 120VAC, 22kA, plug in, combo ARC fault, pigtail

QO120VHCAFI

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 534.00 USD

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A
Voltage Rating	120 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Circuit Breaker Type	Combination ARC-fault
Ratings	HACR rated
Electrical Connection	Pressure plate
Connections Terminals	Pigtail neutral

Complementary

Interrupt Rating	22 kA 120 V AC
Number Of Panel Spaces	1
Wire Size	AWG 14...AWG 8 copper AWG 12...AWG 8 aluminium
Height	4.76 in (121 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.56 lb(US) (0.254 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US1DE2A06303
Discount Schedule	DE2A
Gtin	785901709831
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	MX
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.40 in (3.556 cm)
Package 1 Width	4.20 in (10.668 cm)
Package 1 Length	5.60 in (14.224 cm)
Package 1 Weight	8.96 oz (254.012 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov