

# Product data sheet

## Characteristics

# QO130L200PGC

QO LoadCTR, Main Lugs, 200A, 1PH-3W, 30SP, NEMA1, Incl. Gnd.Bar, PON, Comb. CV

Product availability : Stock - Normally stocked in distribution facility



Price\* : 684.00 USD



### Main

|  |             |
|--|-------------|
| Product                                | Load Center |
| Marketing Trade Name                   | QO          |
| Load center type                       | Main lugs   |
| Line Rated Current                     | 200 A       |
| Number of spaces                       | 30          |
| Short Circuit Current Rating           | 65 kA       |
| Maximum Number of Single Pole Circuits | 30          |
| Maximum Number of Tandem Breakers      | 0           |
| Phase                                  | 1 phase     |

### Complementary

|                        |  |
|------------------------|--|
| Wire Size              | AWG 6...250 kcmil (aluminium/copper)   |
| Enclosure Rating       | NEMA 1 indoor                          |
| Cover type             | Combination flush/surface cover        |
| Grounding Bar          | Grounding bar included (not installed) |
| Electrical connection  | Lugs                                   |
| Wiring configuration   | 3-wire                                 |
| Busbar Material        | Tin plated copper busbar               |
| Enclosure Material     | Welded sheet steel                     |
| Cover Finish           | Baked enamel grey                      |
| Box number             | 9                                      |
| Product certifications | UL listed                              |
| Height                 | 29.84 in (758 mm)                      |
| Width                  | 14.25 in (362 mm)                      |

## Ordering and shipping details

|                       |  |
|-----------------------|--|
| Category              | 10003 - QO PON 1PH LC,12-60 CKT, ML N1 |
| Discount Schedule     | DE3A                                   |
| GTIN                  | 00785901976448                         |
| Nbr. of units in pkg. | 1                                      |
| Package weight(Lbs)   | 26.879999999999999                     |
| Returnability         | Y                                      |
| Country of origin     | US                                     |

## Offer Sustainability

|                                  |   |
|----------------------------------|---|
| RoHS (date code: YYWW)           | Compliant<br><a href="#">Schneider Electric declaration of conformity</a>   |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>          |
| Product end of life instructions | Need no specific recycling operations   |
| California proposition 65        | WARNING: This product can expose you to chemicals including:  |
| ----- Substance 1                | Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| ----- More information           | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                   |