





Load center, QO, 1 phase, 30 spaces, 30 circuits, 200A convertible main lugs, PoN, NEMA1, Qwik-grip, gnd bar, UL

QO130L200PQG

Product availability: Stock - Normally stocked in distribution facility

Price*: 644.76 USD

Main

Marketing Trade Name	QO
Product Type	Load Center
Provided Equipment	Qwik grip assembly kit 1)

Complementary

Tightening Torque	Main lugs 250 lb.in, AWG 4250 kcmil, aluminium/copper	
Pon Convertible Mains (Lugs)	PoN Convertible Mains (lugs)	
Rated Current	200 A	
Number Of Spaces	30	
Max Short Circuit Current Rating	65 kA	
Maximum Number Of Single Pole Circuits	40	
Maximum Number Of Tandem Breakers	dem 10	
Number Of Phases	1 phase	
Voltage Rating	120/240 V AC	
Wire Size	AWG 6300 kcmil aluminium/copper	
Ground Bar	Grounding bar included (not installed)	
Busbar Material	Copper: busbar	
Enclosure Material	Welded sheet steel	
Surface Finish	Baked enamel Gray	
Box Number	9Q	
Height	29.84 in (758 mm)	
Width	14.25 in (362 mm)	

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	US1DE3A10003
Discount Schedule	DE3A
Gtin	785901774341
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.00 in (10.16 cm)
Package 1 Width	14.44 in (36.672 cm)
Package 1 Length	30.88 in (78.423 cm)
Package 1 Weight	16.83 lb(US) (7.634 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
②	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov