





Load center, QO, 1 phase, 40 spaces, 60 circuits, 225A convertible main breaker, PoN, NEMA1, UL

QO140M225P

____(

! Discontinued on: Jun 30, 2023

① Discontinued

Product availability: Stock - Normally stocked in distribution facility

Main

Marketing Trade Name	QO
Product Type	Load Center

Complementary

Tightening Torque	Cover 20 lb.in	
Pon Convertible Mains (Lugs)	PoN Convertible Mains (breaker)	
Rated Current	225 A	
Number Of Spaces	40	
Max Short Circuit Current Rating	22 kA	
Maximum Number Of Single Pole Circuits	40	
Maximum Number Of Tandem Breakers	20	
Number Of Phases	1 phase	
Ground Bar	Grounding bar (ordered separately)	
Box Number	11	
Height	37.99 in (965 mm)	
Width	14.25 in (362 mm)	
Depth	3.74 in (95 mm)	
Net Weight	22.33 lb(US) (10.130 kg)	

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	US1DE3A10001
Discount Schedule	DE3A
Gtin	785901617143

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	14.25 in (36.2 cm)
Package 1 Length	37.99 in (96.5 cm)
Package 1 Weight	15.00 lb(US) (6.804 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov