





Load center, QO, 1 phase, 42 spaces, 42 circuits, 200A convertible main breaker, PoN, NEMA1, 3 x QO115PCAFI, value pack

QO142M200PCAFVP



(!) Discontinued on: Jun 30, 2023

Product availability: Stock - Normally stocked in distribution facility

Main

Marketing Trade Name	QO
Product Type	Load Center
Device Application	Value pack
Cover Type	Combination flush/surface cover

Complementary

Tightening Torque	Cover 20 lb.in	
Pon Convertible Mains (Lugs)	PoN Convertible Mains (breaker)	
Number Of Spaces	42	
Maximum Number Of Single Pole Circuits	42	
Number Of Phases	1 phase	
Ground Bar	Grounding bar (ordered separately)	
Box Number	11R	
Height	37.98 in (964.69 mm)	
Width	14.625 in (371.48 mm)	
Depth	4.1875 in (106.36 mm)	

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	US1DE3A00184
Discount Schedule	DE3A
Gtin	785901809364
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	5.70 in (14.478 cm)	
Package 1 Width	16.20 in (41.148 cm)	
Package 1 Length	40.70 in (103.378 cm)	
Package 1 Weight	39.35 lb(US) (17.849 kg)	
Unit Type Of Package 2	PAL	
Number Of Units In Package 2	18	
Package 2 Height	39.50 in (100.33 cm)	
Package 2 Width	40.70 in (103.378 cm)	
Package 2 Length	48.00 in (121.92 cm)	
Package 2 Weight	739.00 lb(US) (335.204 kg)	



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov