# Product data sheet

Specifications



### Mini circuit breaker, QO, 15A, 1 pole, 120/240VAC, 10kA, plug in, consumer pack, barcode label

QO115CP1235

Discontinued on: Mar 7, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	15 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR and Switching Duty rated
Electrical Connection	Pressure plate
Type Of Packing	Consumer packaging

### Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 120 V AC
Number Of Panel Spaces	1
Wire Size	AWG 14AWG 8 copper or aluminium
Tightening Torque	35.40 lbf.in (4 N.m)
Height	2.99 in (76 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.27 lb(US) (0.122 kg)

#### Environment

Certifications	UL Listed CSA	
Ambient Rating	104 °F (40 °C)	

### Ordering and shipping details

Category	US1DE2A00004
Discount Schedule	DE2A
Gtin	785901136392

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	US

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.70 in (1.778 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.20 in (8.128 cm)
Package 1 Weight	4.32 oz (122.47 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	8.00 in (20.32 cm)
Package 2 Width	6.70 in (17.018 cm)
Package 2 Length	17.40 in (44.196 cm)
Package 2 Weight	29.09 lb(US) (13.193 kg)

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations