





Mini circuit breaker, QO, 15A, 1 pole, 120VAC, 10kA, plug in, 6mA grd fault A, pigtail, consumer pack

QO115GFICP

Product availability: Stock - Normally stocked in distribution

Price*: 233.00 USD

Main

Product	Miniature circuit-breaker	
Range	QO	
Current Rating	15 A	
Voltage Rating	120 V AC	
Mounting Type	Plug-in	
Number Of Poles	1P	
Circuit Breaker Type	Ground fault protecting class A 6 mA	
Ratings	Not rated	
Electrical Connection	Pressure plate	
Type Of Packing	Consumer packaging	

Complementary

Interrupt Rating	10 kA 120 V AC
Number Of Panel Spaces	1
Wire Size	AWG 14AWG 8 copper AWG 12AWG 8 aluminium
Tightening Torque	35.40 lbf.in (4 N.m) 40.71 lbf.in (4.6 N.m) 0.010.03 in² (420 mm²) (AWG 12AWG 4)
Height	4.13 in (105 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.60 lb(US) (0.272 kg)

Environment

Certifications	UL Listed CSA	
Ambient Rating	104 °F (40 °C)	

Ordering and shipping details

Category	US10CPQ01301
Discount Schedule	0CPQ
Gtin	047569522314

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes
Country Of Origin	US

Packing Units

PCE
1
1.30 in (3.302 cm)
4.50 in (11.43 cm)
7.90 in (20.066 cm)
9.60 oz (272.155 g)
CAR
3
8.30 in (21.082 cm)
4.90 in (12.446 cm)
4.00 in (10.16 cm)
30.40 oz (861.825 g)
PAL
360
40.00 in (101.6 cm)
40.00 in (101.6 cm)
48.00 in (121.92 cm)
220.00 lb(US) (99.79 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov