





Load center, QO, 1 phase, 24 spaces, 36 circuits, 150A convertible main breaker, PoN, NEMA1, UL

QO124M150P

Product availability: Stock - Normally stocked in distribution facility

Price*: 972.00 USD

Main

Marketing Trade Name	QO	
Product Type	Load Center	

Complementary

Tightening Torque	Cover 20 lb.in
Pon Convertible Mains (Lugs)	PoN Convertible Mains (breaker)
Rated Current	150 A
Number Of Spaces	24
Max Short Circuit Current Rating	22 kA
Maximum Number Of Single Pole Circuits	36
Maximum Number Of Tandem Breakers	12
Number Of Phases	1 phase
Ground Bar	Grounding bar (ordered separately)
Box Number	9
Height	29.84 in (758 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)
Net Weight	25.99 lb(US) (11.790 kg)

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	US1DE3A10001
Discount Schedule	DE3A
Gtin	785901609650
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.41 in (11.2 cm)
Package 1 Width	14.72 in (37.4 cm)
Package 1 Length	31.10 in (79.0 cm)
Package 1 Weight	18.50 lb(US) (8.39 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
②	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov