





Mini circuit breaker, QO, 30A, 1 pole, 120VAC, 10kA, plug in, 30mA grd fault B, aux switch 1B

QO130EPD1201

- ! Discontinued on: Dec 8, 2020
- ! End-of-service on: Dec 31, 2020

① Discontinued

Main

Product	Miniature circuit-breaker	
Range	QO	
Current Rating	30 A	
Voltage Rating	120 V AC	
Mounting Type	Plug-in	
Number Of Poles	1P	
Circuit Breaker Type	Ground fault protecting class B 30 mA	
Ratings	Not rated	
Electrical Connection	Pressure plate	
Options	Auxiliary switch 120 V AC 1B	

Complementary

Interrupt Rating	10 kA 120 V AC
Number Of Panel Spaces	2
Wire Size	AWG 14AWG 8 copper AWG 12AWG 8 aluminium
Tightening Torque	35.40 lbf.in (4 N.m) 40.71 lbf.in (4.6 N.m) 0.010.03 in² (420 mm²) (AWG 12AWG 4)
Height	4.13 in (105 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.75 lb(US) (0.340 kg)

Environment

Certifications	UL Listed CSA	
Ambient Rating	104 °F (40 °C)	

Ordering and shipping details

Category	00910-QO-EPD,QOB-EPD BREAKERS	
Discount Schedule	DE2A	
Gtin	00785901706427	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	12.00 oz (340.194 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov