SQUARE D





Mini circuit breaker, QO, 30A, 1 pole, 120VAC, 10kA, plug in, 6mA grd fault A, pigtail, consumer pack

QO130GFICP

Discontinued on: Oct 18, 2021

(!) Discontinued

### Main

Product	Miniature circuit-breaker	
Range	QO	
Current Rating	30 A	
Voltage Rating	120 V AC	
Mounting Type	Plug-in	
Number Of Poles	1P	
Circuit Breaker Type	Ground fault protecting class A 6 mA	
Ratings	Not rated	
Electrical Connection	Pressure plate	
Type Of Packing	Consumer packaging	

## Complementary

Interrupt Rating	10 kA 120 V AC	
Number Of Panel Spaces	1	
Wire Size	AWG 14AWG 8 copper AWG 12AWG 8 aluminium	
Tightening Torque	35.40 lbf.in (4 N.m) 40.71 lbf.in (4.6 N.m) 0.010.03 in² (420 mm²) (AWG 12AWG 4)	
Height	4.13 in (105 mm)	
Width	0.75 in (19 mm)	
Depth	2.91 in (74 mm)	
Net Weight	0.54 lb(US) (0.245 kg)	

## **Environment**

Certifications	UL Listed CSA	
Ambient Rating	104 °F (40 °C)	

## Ordering and shipping details

Category	01301-QO-GFI BRKRS 1 POLE	
Discount Schedule	CPQ	
Gtin	00047569570278	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	MX

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.20 in (3.048 cm)
Package 1 Width	4.50 in (11.43 cm)
Package 1 Length	7.90 in (20.066 cm)
Package 1 Weight	8.64 oz (244.94 a)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	End of Life Information