





Load center, QO, 1 phase, 32 spaces, 38 circuits, 100A convertible main breaker, PoN, NEMA1, UL

QO132M100P

Product availability: Stock - Normally stocked in distribution facility

Price*: 909.00 USD

Main

Marketing Trade Name	QO
Product Type	Load Center

Complementary

Tightening Torque	Cover 20 lb.in	
Pon Convertible Mains (Lugs)	PoN Convertible Mains (breaker)	
Rated Current	100 A	
Number Of Spaces	32	
Max Short Circuit Current Rating	22 kA	
Maximum Number Of Single Pole Circuits	38	
Maximum Number Of Tandem Breakers	6	
Number Of Phases	1 phase	
Ground Bar	Grounding bar (ordered separately)	
Box Number	8	
Height	26.02 in (661 mm)	
Width	14.25 in (362 mm)	
Depth	3.74 in (95 mm)	
Net Weight	15.54 lb(US) (7.050 kg)	

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	US1DE3A10001
Discount Schedule	DE3A
Gtin	785901611271
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	14.25 in (36.2 cm)
Package 1 Length	26.02 in (66.1 cm)
Package 1 Weight	16.00 lb(US) (7.258 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov