

Product data sheet

Specifications



Mini circuit breaker, QO, 40A, 1 pole, 120/240VAC, 10kA, plug in, aux switch 1A

QO1401200

Discontinued on: Aug 25, 2023

Discontinued

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	40 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Options	Auxiliary switch 120 V AC 1A

Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 120 V AC
Number Of Panel Spaces	2
Wire Size	AWG 8...AWG 2 copper or aluminium
Tightening Torque	44.25 lbf.in (5 N.m)
Height	3.11 in (79 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	1.00 lb(US) (0.454 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00004-QO,QOT 10-30A 1P;10-60A 2P
Discount Schedule	DE2A
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	MX
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.00 in (7.62 cm)
Package 1 Width	1.47 in (3.734 cm)
Package 1 Length	3.31 in (8.407 cm)
Package 1 Weight	0.16 oz (4.536 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
<hr/>		
Eu Rohs Directive		Compliant
		EU RoHS Declaration
<hr/>		
China Rohs Regulation		China RoHS declaration
		Pro-active China RoHS declaration (out of China RoHS legal scope)