Product data sheet

Specifications







Tandem mini circuit breaker, QO, 1 x 1 pole at 15A, 1 x 1 pole at 20A, 120/240VAC, 10kA, plug in

QO1520

Product availability: Stock - Normally stocked in distribution facility

Price*: 73.00 USD

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A 15 A
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Circuit Breaker Type	Tandem
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

• •	
Interrupt Rating	10 kA 120/240 V AC
Number Of Panel Spaces	1
Wire Size	AWG 14AWG 8 copper or aluminium
Tightening Torque	24.78 lbf.in (2.8 N.m)
Height	3.23 in (82 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.35 lb(US) (0.159 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US1DE2A00181
Discount Schedule	DE2A
Gtin	785901400929
Returnability	Yes

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country Of	Origin	
------------	--------	--

Packing Units

r aoning onito	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.70 in (1.778 cm)
Package 1 Width	3.20 in (8.128 cm)
Package 1 Length	3.20 in (8.128 cm)
Package 1 Weight	5.60 oz (158.757 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3.80 in (9.652 cm)
Package 2 Width	2.80 in (7.112 cm)
Package 2 Length	7.60 in (19.304 cm)
Package 2 Weight	3.26 lb(US) (1.479 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	8.30 in (21.082 cm)
Package 3 Width	19.60 in (49.784 cm)
Package 3 Length	8.20 in (20.828 cm)
Package 3 Weight	34.30 lb(US) (15.558 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations