Product data sheet

Specifications





Mini circuit breaker, QO, 15A, 2 pole, 120/240VAC, 10kA, plug in

QO215

Product availability: Stock - Normally stocked in distribution facility

Price*: 67.00 USD

Main

Miniature circuit-breaker QO 15 A
15 A
120/240 V AC 120 V AC
Plug-in
2P
Standard
HACR rated
Pressure plate

Complementary

Interrupt Rating	10 kA 120/240 V AC
	10 kA 120 V AC
Number Of Panel Spaces	2
Wire Size	AWG 14AWG 8 copper or aluminium
Tightening Torque	35.40 lbf.in (4 N.m)
Height	3.11 in (79 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.60 lb(US) (0.272 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US1DE2A00004
Discount Schedule	DE2A
Gtin	785901400301
Returnability	Yes
Country Of Origin	МХ

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.50 in (3.81 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.30 in (8.382 cm)
Package 1 Weight	8.64 oz (244.94 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	3.30 in (8.382 cm)
Package 2 Width	2.70 in (6.858 cm)
Package 2 Length	7.70 in (19.558 cm)
Package 2 Weight	2.72 lb(US) (1.234 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	50
Package 3 Height	8.40 in (21.336 cm)
Package 3 Width	7.40 in (18.796 cm)
Package 3 Length	17.50 in (44.45 cm)
Package 3 Weight	28.05 lb(US) (12.723 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
 Mercury Free
 Rohs Exemption Information Yes
 Halogen Free Product

Certifications & Standards

California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Circularity Profile	No need of specific recycling operations
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Eu Rohs Directive	Compliant with Exemptions
Reach Regulation	REACh Declaration