# Product data sheet

Specifications



# Mini circuit breaker, QO, 15A, 2 pole, 120/240VAC, 10kA, plug in, clam

QO215C

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 460.00 USD

#### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	15 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate
Type Of Packing	Clam packaging

## Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 120 V AC	
Number Of Panel Spaces	2	
Wire Size	AWG 14AWG 8 copper or aluminium	
Tightening Torque	35.40 lbf.in (4 N.m)	
Height	2.99 in (76 mm)	
Width	1.50 in (38 mm)	
Depth	2.91 in (74 mm)	
Net Weight	0.58 lb(US) (0.263 kg)	

### Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	US10CPQ01342
Discount Schedule	0CPQ
Gtin	047569522161

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	Yes		
Country Of Origin	MX		
Packing Units			

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.60 in (4.064 cm)
Package 1 Width	4.40 in (11.176 cm)
Package 1 Length	4.40 in (11.176 cm)
Package 1 Weight	9.28 oz (263.084 g)

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.	
Circularity Profile	No need of specific recycling operations	