Product data sheet

Specifications



Meter mains, QO, CSED, ringless socket, 400A, surface mount, maximum 12 spaces, Class 320 with lever bypass

QU12L400CL

() Discontinued on: Sep 15, 2023

(!) To be end-of-service on: Dec 31, 2024

Product availability: Stock - Normally stocked in distribution facility

Main

Product Or Component Type	Meter Mains
Range Of Product	QO
Includes	Fifth jaw

Complementary

Complementary	
Line Rated Current	400 A
Short-Circuit Current	25 kA
Network Number Of Phases	1
Meter Socket Type	Ringless
Mounting	Surface Semi flush with field installed flange kit
Number Of Spaces	12
Number Of Circuits	0
Number Of Tandem Breakers	0
Ниb Туре	A-L
Electrical Connection	Lugs, service ground Studs, line side
Wire Size	AWG 4250 kcmil aluminium)service ground AWG 4250 kcmil copper)service ground
Disconnect	Service disconnect (factory installed) Service disconnect (ordered separately)
Main Breaker Rating	200 A
Service Feed Location	UG
Bypass Type	Class 320 lever bypass
Height	43.00 in (1092.20 mm)
Width	28.25 in (717.55 mm)
Depth	7.87 in (199.90 mm)
Bus Rating	200.0 A

Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US1DE3A00022
Discount Schedule	DE3A
Gtin	785901421009
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.61 in (24.4 cm)
Package 1 Width	29.29 in (74.4 cm)
Package 1 Length	42.28 in (107.4 cm)
Package 1 Weight	112.00 lb(US) (50.802 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov