

# Product data sheet

Specifications



## Electrode holder for liquid level control, Harmony, use up to 350 degree C

RM79696006

 **Discontinued on:** Oct 9, 2023

 **Discontinued**

**Product availability: Non-Stock - Not normally stocked in distribution facility**

### Main

Range Of Product	Harmony Control Relays
Product Or Component Type	Level electrode holder
Accessory / Separate Part Designation	Electrode for use up to 350 °C
Accessory / Separate Part Destination	Liquid level control relay
Accessory / Separate Part Category	Relay accessories
Maximum Pressure	<= 15 kg/cm²

### Complementary

Material	Ceramic isolation Stainless steel
Thread Type	3/8 BSP
Net Weight	0.33 lb(US) (0.15 kg)

### Environment

Maximum Ambient Air Temperature For Operation	662 °F (350 °C)
---	-----------------

### Ordering and shipping details

Category	US10CP222380
Discount Schedule	0CP2
Gtin	3389110281750
Returnability	No
Country Of Origin	FR

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.98 in (2.5 cm)
Package 1 Width	1.57 in (4.0 cm)
Package 1 Length	3.46 in (8.8 cm)
Package 1 Weight	2.47 oz (70.0 g)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	S01
Number Of Units In Package 2	14
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	2.68 lb(US) (1.214 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)