





# Mini circuit breaker, QO, 16A, 3 pole, 240/415VAC, 3kA, plug in

QOXD316

- ! Discontinued on: Feb 17, 2021
- ! End-of-service on: Mar 15, 2021



Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	16 A
Voltage Rating	240/415 V AC
Mounting Type	Plug-in
Number Of Poles	3P
Circuit Breaker Type	Standard

#### Complementary

Interrupt Rating	Icu 3 kA 240/415 V AC IEC 947-2
Number Of Panel Spaces	3
Tightening Torque	44.25 lbf.in (5 N.m) 0.020.04 in² (1025 mm²) (AWG 8AWG 2)
Height	2.99 in (76 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	0.86 lb(US) (0.390 kg)

#### **Environment**

Certifications	IEC
Ambient Rating	104 °F (40 °C)

# Ordering and shipping details

Category	US1DE2A00920
Discount Schedule	DE2A
Gtin	785901430506
Returnability	No
Country Of Origin	US

#### **Packing Units**

Unit Type Of Package 1	PCF	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	3.40 in (8.636 cm)
Package 1 Width	2.30 in (5.842 cm)
Package 1 Length	4.00 in (10.16 cm)
Package 1 Weight	13.76 oz (390.089 g)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

<b>⊘</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Product	

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations