





All in one, Homeline, combination service entrance, ringless socket, 200A, surface, 30 spaces, 42 circuits, 22kA SCCR, OH, UG, no bypass, PON

RC3042M200PS

Product availability: Stock - Normally stocked in distribution facility

Price*: 2,058.00 USD

Main

Product Or Component Type	All-In-One
Range Of Product	Homeline
Meter Socket Type	Ringless
Hub Type	A

Complementary

Line Rated Current	200 A
Short-Circuit Current	22 kA
Mounting	Surface
Number Of Spaces	30
Number Of Circuits	42
Number Of Tandem Breakers	12
Electrical Connection	Lugs, line side Lugs, service ground
Wire Size	AWG 6350 kcmil (aluminium/copper) line side AWG 12AWG 2/0 (aluminium/copper) service ground
Tightening Torque	Main lugs 250 lb.in, AWG 6350 kcmil, aluminium/copper Service ground 50 lb.in, AWG 3AWG 2/0, aluminium/copper Service ground 45 lb.in, AWG 6AWG 4, aluminium/copper Service ground 40 lb.in, AWG 8, aluminium/copper Branch lugs 35 lb.in, AWG 6AWG 4, aluminium/copper Branch lugs 25 lb.in, AWG 8, aluminium/copper Branch lugs 20 lb.in, AWG 14AWG 10, aluminium/copper Branch lugs 20 lb.in, AWG 12AWG 10, aluminium/copper Cover 10 lb.in
Disconnect	Service disconnect (factory installed)
Disconnect Rating	200 A
Branch Breaker Rating	200 A
Service Feed Location	OH UG
Bypass Type	No bypass
Connections - Terminals	Plug-on neutral
Width	18.76 in (476.50 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Depth	5.41 in (137.41 mm)
Height	45.47 in (1154.94 mm)
Bus Rating	200.0 A

Environment

Nema Rating NEMA 3R

Ordering and shipping details

_	
Category	US1DE3A00148
Discount Schedule	DE3A
Gtin	785901009733
Returnability	Yes
Country Of Origin	MX

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.01 in (17.8 cm)
Package 1 Width	19.49 in (49.5 cm)
Package 1 Length	50.00 in (127.0 cm)
Package 1 Weight	69.55 lb(US) (31.547 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	10
Package 2 Height	37.50 in (95.25 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	50.00 in (127.0 cm)
Package 2 Weight	723.00 lb(US) (327.947 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov