

(!) Discontinued

Meter mains, Homeline, CSED, ringless socket, 200A, outdoor surface mount, maximum 8 spaces, 16 circuits, lever bypass

RC816F200SL

- Discontinued on: Sep 15, 2023
- ! To be end-of-service on: Dec 31, 2024

Product availability: Stock - Normally stocked in distribution facility

#### Main

Product Or Component Type	Meter Mains
Range Of Product	Homeline

### Complementary

Line Rated Current	200 A
Short-Circuit Current	22 kA
Network Number Of Phases	1
Meter Socket Type	Ringless
Mounting	Surface (outdoor)
Number Of Spaces	8
Number Of Circuits	16
Number Of Tandem Breakers	8
Hub Type	A
Electrical Connection	Feed-thru lugs, service ground Feed-thru lugs, line side
Wire Size	AWG 8AWG 2/0 aluminium/copper)service ground AWG 6350 kcmil aluminium/copper)line side
Tightening Torque	Main lugs 250 lb.in, AWG 6350 kcmil, aluminium/copper Service ground 50 lb.in, AWG 14AWG 2/0, copper Service ground 50 lb.in, AWG 12AWG 2/0, aluminium Branch lugs 35 lb.in, AWG 6AWG 4, aluminium/copper Branch lugs 25 lb.in, AWG 8, aluminium/copper Branch lugs 20 lb.in, AWG 14AWG 10, copper Branch lugs 20 lb.in, AWG 12AWG 10, aluminium Cover 10 lb.in
Disconnect	Service disconnect (factory installed)
Main Breaker Rating	200 A
Branch Breaker Rating	200 A
Service Feed Location	OH UG
Bypass Type	Class 320 lever bypass
Height	48.62 in (1234.95 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	18.35 in (466.09 mm)
Depth	5.32 in (135.13 mm)
Bus Rating	200 0 A

### **Environment**

Product Certifications UL E-6294

## Ordering and shipping details

e i e		
Category	US1DE3A00048	
Discount Schedule	DE3A	
Gtin	785901976615	
Returnability	Yes	
Country Of Origin	US	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.00 in (17.78 cm)
Package 1 Width	19.50 in (49.53 cm)
Package 1 Length	50.00 in (127.0 cm)
Package 1 Weight	76.05 lb(US) (34.496 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	12
Package 2 Height	43.50 in (110.49 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	49.50 in (125.73 cm)
Package 2 Weight	952.00 lb(US) (431.82 kg)

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov