Product data sheet

Specifications

SQUARE 🗩





All in one, Homeline, CSED, ringless socket, 400A, surface/ semi mount, 30 spaces, 40 circuits, 25kA SCCR, 320 lever bypass

RU3040D400CL

Product availability: Stock - Normally stocked in distribution facility

Price*: 6,993.00 USD

Main

Product Or Component Type	All-In-One
Range Of Product	Homeline
Meter Socket Type	Ringless
Hub Type	A-L

Complementary

e emprementar j	
Line Rated Current	400 A
Short-Circuit Current	25 kA
Mounting	Surface Semi flush with field installed flange kit
Number Of Spaces	30
Number Of Circuits	40
Number Of Tandem Breakers	10
Electrical Connection	Lugs, service ground Studs, line side
Wire Size	AWG 4250 kcmil (aluminium) service ground AWG 4250 kcmil (copper) service ground
Disconnect	Service disconnect (factory installed)
Disconnect Rating	200 A
Branch Breaker Rating	200 A
Service Feed Location	UG
Bypass Type	Class 320 lever bypass
Width	28.25 in (717.55 mm)
Depth	7.87 in (199.90 mm)
Height	43.00 in (1092.20 mm)
Bus Rating	200.0 A

Ordering and shipping details

Category

US1DE3A00148

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Discount Schedule	DE3A
Gtin	785901445432
Returnability	Yes
Country Of Origin	МХ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.00 in (25.4 cm)
Package 1 Width	29.29 in (74.4 cm)
Package 1 Length	42.52 in (108.0 cm)
Package 1 Weight	112.00 lb(US) (50.802 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov