

Product data sheet

Specifications



Surge protection device,
Surgelogic, 120kA, 480Y/277
VAC, 3 phase, 4 wire, NEMA 1,
disconnect switch

SSP04EMA12D

Product availability: Stock - Normally stocked in distribution facility

Price*: 5,311.23 USD

Main

Product	Surge protection device
Range	Surgelogic
Device Short Name	EMA

Complementary

Voltage Rating	480Y/277 V AC
Mcov	320 V
Sccr	200 kA
Surge Current	120 kA
Nominal Discharge Current	20 kA
Rated Current	150 A
Number Of Phases	3 phase
Max Number Of Poles	3
Wiring Configuration	4-wire
Connection	Lugs AWG 10...AWG 3/0 copper 35.40 lbf.in (4 N.m)
Local Signalling	Status LED green per phase normal operation Status LED red per phase fault
Provided Equipment	Alarm enable/disable switch Switch-disconnector Surge counter Dry contacts
Cable Length	19.02 in (483 mm)
Device Mounting	Surface
Height	19.49 in (495 mm)
Width	9.88 in (251 mm)
Depth	5.31 in (135 mm)

Environment

Ambient Operating	149 °F (65 °C)
Enclosure Rating	NEMA 1
Enclosure Material	Gray painted sheet steel

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	CSA C22.2 No 8 UL 1449:ed. 4 UL 1283:ed. 5
-----------	--

Ordering and shipping details

Category	US1DE1B08464
Discount Schedule	DE1B
Gtin	785901075387
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.49 in (49.5 cm)
Package 1 Width	9.88 in (25.1 cm)
Package 1 Length	5.31 in (13.5 cm)
Package 1 Weight	20.50 lb(US) (9.299 kg)

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov