Product data sheet

Specifications





① Discontinued

Contactor, Tesys N Contactors, nonreversing, 3P, 3phase, 9A, 2HP at 460VAC, NEMA size 00, 480VAC 50/60Hz coil, open

T02AN13T7

- ! Discontinued on: Sep 15, 2023
- (1) To be end-of-service on: Dec 31, 2024

Product availability: Stock - Normally stocked in distribution facility

Main

Product Type	Contactor
Range	TeSys N
Contactor Type	Non-reversing
Nema Size	00
Motor Horsepower Rating Hp	1.5 hp 200 V AC
	1.5 hp 230 V AC
	2 hp 460 V AC
	2 hp 575 V AC

Complementary

Rated Current	9 A
[Ue] Rated Operational Voltage	600 V AC
Network Phases	3 phase
Number Of Poles	3P
Control Circuit	Common control circuit
Coil Volltage	480 V AC
Auxiliary Contact Composition	1 NO + 1 NC
Electrical Connection	Screw clamp terminals
Height	3.34 in (84.84 mm)
Width	1.76 in (44.70 mm)
Depth	3.66 in (92.96 mm)
Product Weight	0.91 lb(US) (0.41 kg)

Environmental

Product Certifications	UL Listed CSA
Nema Degree Of Protection	Not rated (open device)

Ordering and shipping details

Category US10CP121196

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	0CP1	
Gtin	3606480572999	
Returnability	No	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.70 in (11.94 cm)
Package 1 Width	3.70 in (9.4 cm)
Package 1 Length	2.10 in (5.33 cm)
Package 1 Weight	0.90 lb(US) (0.41 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov