# Product data sheet





Contactor, Tesys N Contactors, nonreversing, 3P, 3phase, 18A, 5HP at 460VAC, NEMA size 0, 120VAC 50/60Hz coil, open

T02BN13G7

Product availability: Stock - Normally stocked in distribution facility

Price\*: 280.00 USD

#### Main

Product Type	Contactor
Range	TeSys N
Contactor Type	Non-reversing
Nema Size	0
Motor Horsepower Rating Hp	3 hp 200 V AC
	3 hp 230 V AC
	5 hp 460 V AC
	5 hp 575 V AC

### Complementary

Rated Current	18 A
[Ue] Rated Operational Voltage	600 V AC
Network Phases	3 phase
Number Of Poles	3P
Control Circuit	Common control circuit
Coil Volltage	120 V AC
Auxiliary Contact Composition	1 NO + 1 NC
Electrical Connection	Screw clamp terminals
Height	3.34 in (84.84 mm)
Width	1.76 in (44.70 mm)
Depth	3.66 in (92.96 mm)
Product Weight	0.91 lb(US) (0.41 kg)

## **Environmental**

Product Certifications	UL Listed CSA
Nema Degree Of Protection	Not rated (open device)

## Ordering and shipping details

Category	US10CP121196
Discount Schedule	0CP1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	3606480573101
Returnability	Yes
Country Of Origin	FR

# **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.0 cm)
Package 1 Width	3.54 in (9.0 cm)
Package 1 Length	4.33 in (11.0 cm)
Package 1 Weight	0.91 lb(US) (0.413 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>②</b>	Reach Free Of Svhc
	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
End of Life Information
WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov