# Product data sheet

(!) Di

Specifications





# NEMA Contactor, TeSys N, reversing, Size 0, 18A, 5HP at 460VAC, 3 pole, 3 phase, 480VAC 50/60Hz coil, open

T02BN23T7

scontinued	

Discontinued on: Sep 15, 2023

(!) To be end-of-service on: Dec 31, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Type	Contactor
Range	TeSys N
Contactor Type	Reversing
Nema Size	0
Motor Horsepower Rating Hp	3 hp 200 V AC 3 hp 230 V AC 5 hp 460 V AC 5 hp 575 V AC

### Complementary

Rated Current	18 A
[Ue] Rated Operational Voltage	600 V AC
Network Phases	Common control circuit
Number Of Poles	480 V AC
Control Circuit	3P
Coil Volltage	3 phase
Auxiliary Contact Composition	1 NO + 1 NC
Electrical Connection	Screw clamp terminals

### Environmental

Product Certifications	UL Listed CSA
Nema Degree Of Protection	Not rated (open device)

### Ordering and shipping details

Category	US10CP121196
Discount Schedule	0CP1
Gtin	3606480573170
Returnability	No
Country Of Origin	FR

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.29 in (10.9 cm)
Package 1 Width	4.49 in (11.4 cm)
Package 1 Length	4.65 in (11.8 cm)
Package 1 Weight	1.80 lb(US) (0.815 kg)

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov