Product data sheet

Specifications





NEMA Contactor, TeSys N, reversing, Size 0, 18A, 5HP at 460VAC, 3 pole, 3 phase, 240VAC 50/60Hz coil, open

T02BN23U7

① Discontinued

- ! Discontinued on: Nov 11, 2020
- ! End-of-service on: Dec 31, 2020

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Type	Contactor	
Range	TeSys N	
Contactor Type	Reversing	
Nema Size	0	
Motor Horsepower Rating Hp	3 hp 200 V AC	
	3 hp 230 V AC	
	5 hp 460 V AC	
	5 hp 575 V AC	

Complementary

Rated Current	18 A	
[Ue] Rated Operational Voltage	600 V AC	
Network Phases	Common control circuit	
Number Of Poles	240 V AC	
Control Circuit	3P	
Coil Volltage	3 phase	
Auxiliary Contact Composition	1 NO + 1 NC	
Electrical Connection	Screw clamp terminals	

Environmental

Product Certifications	UL Listed CSA
Nema Degree Of Protection	Not rated (open device)

Ordering and shipping details

Category	US10CP121196	
Discount Schedule	0CP1	
Gtin	3606480573187	
Returnability	No	
Country Of Origin	FR	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	4.29 in (10.9 cm)	
Package 1 Width	4.49 in (11.4 cm)	
Package 1 Length	4.65 in (11.8 cm)	
Package 1 Weight	1.80 lb(US) (0.815 kg)	



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information Y	res
Ø	Pvc Free	

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov