# Product data sheet

Specifications





# NEMA Contactor, TeSys N, reversing, Size 2, 45A, 25HP at 460VAC, 3 pole, 3 phase, 120VAC 50/60Hz coil, open

T02DN23G7

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 1,500.00 USD

### Main

Product Type	Contactor	
Range	TeSys N	
Contactor Type	Reversing	
Nema Size	2	
Motor Horsepower Rating Hp	10 hp 200 V AC	
	15 hp 230 V AC	
	25 hp 460 V AC	
	25 hp 575 V AC	

## Complementary

Rated Current	45 A
[Ue] Rated Operational Voltage	600 V AC
Network Phases	Common control circuit
Number Of Poles	120 V AC
Control Circuit	3P
Coil Volltage	3 phase
Auxiliary Contact Composition	1 NO + 1 NC
Electrical Connection	Screw clamp terminals

### Environmental

Product Certifications	UL Listed CSA
Nema Degree Of Protection	Not rated (open device)

## Ordering and shipping details

Category	US10CP121196
Discount Schedule	0CP1
Gtin	3606480575129
Returnability	No
Country Of Origin	MX

# **Packing Units**

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.56 in (6.5 cm)
Package 1 Width	5.31 in (13.5 cm)
Package 1 Length	6.10 in (15.5 cm)
Package 1 Weight	4.57 lb(US) (2.074 kg)

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov