# Product data sheet

Specifications





NEMA Contactor, TeSys N, nonreversing, Size 5, 270A, 200HP at 460VAC, 3 pole, 3 phase, 208VAC 50/60Hz coil, open

T02GN13L7

! Discontinued

- Discontinued on: Nov 11, 2020
- ! End-of-service on: Dec 31, 2020

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Type	Contactor	
Range	TeSys N	
Contactor Type	Non-reversing	
Nema Size	5	
Motor Horsepower Rating Hp	75 hp 200 V AC 100 hp 230 V AC 200 hp 460 V AC 200 hp 575 V AC	

### Complementary

Rated Current	270 A
[Ue] Rated Operational Voltage	600 V AC
Network Phases	3 phase
Number Of Poles	3P
Control Circuit	Common control circuit
Coil Volltage	208 V AC
Auxiliary Contact Composition	1 NO
Electrical Connection	Lugs ordered separately
Height	8.11 in (205.99 mm)
Width	8.39 in (213.11 mm)
Depth	8.71 in (221.23 mm)
Product Weight	20.04 lb(US) (9.09 kg)

#### **Environmental**

Product Certifications	UL Listed CSA
Nema Degree Of Protection	Not rated (open device)

## Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	US10CP121197
Discount Schedule	0CP1
Returnability	No
Country Of Origin	LIS

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov