

# Product data sheet

Specifications



Contactor, Tesys N Contactors, nonreversing, 3P, 3phase, 9A, 2HP at 460VAC, NEMA size 00, 120VAC 50/60Hz coil, open

T02AN13G7

Product availability: Stock - Normally stocked in distribution facility

Price\*: 222.00 USD

## Main

|                            |  |
|----------------------------|--|
| Product Type               | Contactor  |
| Range                      | TeSys N  |
| Contactor Type             | Non-reversing  |
| Nema Size                  | 00   |
| Motor Horsepower Rating Hp | 1.5 hp 200 V AC<br>1.5 hp 230 V AC<br>2 hp 460 V AC<br>2 hp 575 V AC |

## Complementary

|                                |                        |
|--------------------------------|------------------------|
| Rated Current                  | 9 A                    |
| [Ue] Rated Operational Voltage | 600 V AC               |
| Network Phases                 | 3 phase                |
| Number Of Poles                | 3P                     |
| Control Circuit                | Common control circuit |
| Coil Voltage                   | 120 V AC               |
| Auxiliary Contact Composition  | 1 NO + 1 NC            |
| Electrical Connection          | Screw clamp terminals  |
| Height                         | 3.34 in (84.84 mm)     |
| Width                          | 1.76 in (44.70 mm)     |
| Depth                          | 3.66 in (92.96 mm)     |
| Product Weight                 | 0.91 lb(US) (0.41 kg)  |

## Environmental

|                           |                         |
|---------------------------|-------------------------|
| Product Certifications    | UL Listed<br>CSA        |
| Nema Degree Of Protection | Not rated (open device) |

## Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US10CP121196 |
| Discount Schedule | 0CP1         |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                   |               |
|-------------------|---------------|
| Gtin              | 3606480572982 |
| Returnability     | Yes           |
| Country Of Origin | US            |

## Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type Of Package 1       | PCE                    |
| Number Of Units In Package 1 | 1                      |
| Package 1 Height             | 1.97 in (5.0 cm)       |
| Package 1 Width              | 3.54 in (9.0 cm)       |
| Package 1 Length             | 4.33 in (11.0 cm)      |
| Package 1 Weight             | 0.91 lb(US) (0.413 kg) |

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

|   |                            |     |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc         |     |
| ✓ | Toxic Heavy Metal Free     |     |
| ✓ | Mercury Free               |     |
| ✓ | Rohs Exemption Information | Yes |
| ✓ | Pvc Free                   |     |

## Certifications & Standards

|                           |   |
|---------------------------|---|
| Reach Regulation          | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive         | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope)   |
| Environmental Disclosure  | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile       | <a href="#">End of Life Information</a>   |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |