

Product data sheet

Specifications



NEMA Contactor, TeSys N,
nonreversing, Size 4, 135A, 100HP
at 460VAC, 3 pole, 3 phase, 24VDC
coil, open

T02FN13BD

! Discontinued

! Discontinued on: Aug 22, 2023

! End-of-service on: Sep 15, 2023

Product availability: Non-Stock - Not normally stocked in
distribution facility

Main

Product Type	Contactor
Range	TeSys N
Contactor Type	Non-reversing
Nema Size	4
Motor Horsepower Rating Hp	40 hp 200 V AC 50 hp 230 V AC 100 hp 460 V AC 100 hp 575 V AC

Complementary

Rated Current	135 A
[Ue] Rated Operational Voltage	600 V AC
Network Phases	3 phase
Number Of Poles	3P
Control Circuit	Common control circuit
Coil Voltage	24 V DC
Auxiliary Contact Composition	1 NO
Electrical Connection	Lugs ordered separately
Height	6.69 in (169.93 mm)
Width	6.44 in (163.58 mm)
Depth	6.68 in (169.67 mm)
Product Weight	9.35 lb(US) (4.24 kg)

Environmental

Product Certifications	UL Listed CSA
Nema Degree Of Protection	Not rated (open device)

Ordering and shipping details

Category	US10CP121197
----------	--------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Discount Schedule	0CP1
Gtin	3606486288313
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	9.35 lb(US) (4.241 kg)

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information.

California Proposition 65

WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov