

Product data sheet

Specifications



NEMA Contactor, TeSys N,
nonreversing, Size 7, 810A, 600HP
at 460VAC, 3 pole, 3 phase,
480VAC 50/60Hz coil, open

T02JN13N7

! Discontinued

! Discontinued on: Nov 11, 2020

! End-of-service on: Dec 31, 2020

Product availability: Non-Stock - Not normally stocked in
distribution facility

Main

Product Type	Contactor
Range	TeSys N
Contactor Type	Non-reversing
Nema Size	7
Motor Horsepower Rating Hp	300 hp 230 V AC 600 hp 460 V AC 600 hp 575 V AC

Complementary

Rated Current	810 A
[Ue] Rated Operational Voltage	600 V AC
Network Phases	3 phase
Number Of Poles	3P
Control Circuit	Common control circuit
Coil Voltage	480 V AC
Auxiliary Contact Composition	1 NO
Electrical Connection	Lugs ordered separately
Height	11.97 in (304.04 mm)
Width	12.17 in (309.12 mm)
Depth	10.05 in (255.27 mm)
Product Weight	41.19 lb(US) (18.68 kg)

Environmental

Product Certifications	UL Listed CSA
Nema Degree Of Protection	Not rated (open device)

Ordering and shipping details

Category	US10CP121197
----------	--------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Discount Schedule	0CP1
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information.

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

California Proposition 65

WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov