

# Product data sheet

Specifications



## TeSys NEMA Sz 2 rev open starter, 3P, 24 VAC, Sprt Ctrl

T36DN23B7S

Discontinued on: Nov 11, 2020

End-of-service on: Dec 31, 2020

Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

|                         |  |
|-------------------------|--|
| Product                 | Starter  |
| Range Of Product        | TeSys N  |
| Current Rating          | 45 A   |
| Certifications          | UL Listed<br>CSA   |
| Control Circuit Type    | Separate control circuit   |
| Enclosure Type          | Not rated (open device)  |
| Auxiliary Contacts      | 1 NO + 1 NC  |
| Horsepower Rating       | 10 HP 200 V AC<br>15 HP 230 V AC<br>25 HP 460 V AC<br>25 HP 575 V AC |
| Number Of Poles         | 3P   |
| Phase                   | 3 phase  |
| Maximum Voltage Rating  | 600 V AC   |
| Nema Size               | 2  |
| Control Circuit Voltage | 24 V AC  |
| Starter Type            | Reversing  |
| Electrical Connection   | Screw clamp terminals  |
| Overload Type           | Solid state Motor Logic class 10/20 15...45 A                        |

### Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US10CP121198 |
| Discount Schedule | 0CP1         |
| Returnability     | No           |
| Country Of Origin | US           |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# Sustainability




**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

|   |  |  |
|---|--|--|
|  | Reach Free Of Svhc   |  |
|  | Mercury Free   |  |
|  | Rohs Exemption Information   | Yes  |
| Eu Rohs Directive   | Compliant  | <a href="#">EU RoHS Declaration</a>  |
| China Rohs Regulation   | <a href="#">China RoHS declaration</a>   | Product out of China RoHS scope. Substance declaration for your information. |
| Weee  | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |  |
| California Proposition 65   | WARNING: Cancer and Reproductive Harm - <a href="#">www.P65Warnings.ca.gov</a>   |  |