

Product data sheet

Specifications



braking resistor - 27 ohm - 200 W -
cable 0.75 m - IP65

VW3A7603R07

Product availability: Non-Stock - Not normally stocked in
distribution facility

Price*: 203.00 USD

Main

Range Of Product	Altivar Lexium
Range Compatibility	Altivar Machine ATV320 Altivar 32 Lexium 15 Lexium 52 Lexium 32 Lexium 32i Lexium 05 Lexium 28 Easy Lexium 16
Product Compatibility	ATV32HU22M2 Variable speed drive ATV320 2.2 kW, 200...240 V, single phase Motion servo drive LXM16D 0.75 kW, 200...230 V, single phase Motion servo drive LXM16D 1 kW, 200...230 V, single phase Motion servo drive LXM16D 1.5 kW, 200...230 V, single phase
Product Or Component Type	Braking resistor
Ohmic Value	27 Ohm

Complementary

Energy Peak	4300 J 480 V 4900 J 400 V 7400 J 230 V 9700 J 115 V
Average Power Available	50 W 122 °F (50 °C)
Continuous Power	200 W
Protection Type	Thermal protection via the servo drive
Net Weight	2.05 lb(US) (0.93 kg)
Cable Length	2.46 ft (0.75 m)

Environment

Ip Degree Of Protection	IP65
Ambient Air Temperature For Storage	-13...185 °F (-25...85 °C)
Ambient Air Temperature For Operation	32...122 °F (0...50 °C)

Ordering and shipping details

Category	US1PC5118263
Discount Schedule	PC51
Gtin	3389119207140

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.77 in (4.500 cm)
Package 1 Width	15.75 in (40.000 cm)
Package 1 Length	5.12 in (13.000 cm)
Package 1 Weight	32.47 oz (920.500 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)


Well-being performance

 Reach Free Of Svhc	
 Mercury Free	
 Rohs Exemption Information	Yes
 Pvc Free	
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Braking Resistor

Dimensions



Dimensions in mm

b	b1	c	c1	H
251	216	15	15.5	204

Dimensions in in.

b	b1	c	c1	H
9.88	8.50	0.59	0.61	8.03