Product data sheet

Specification





graphic display terminal, Altivar, 240 x 160pixels, IP65

VW3A1111

Product availability: Stock - Normally stocked in distribution facility

Price*: 210.00 USD

Main

Range Of Product	Altivar
Range Compatibility	Altivar Process ATV900 Altivar Process ATV600
	Altivar Machine ATV340
Accessory / Separate Part Category	Display and signalling accessories
Accessory / Separate Part Type	Display terminal
Accessory / Separate Part Destination	Variable speed drive
Product Specific Application	To control, adjust and configure the drive
	To save and download configurations
	To display the current values
Ip Degree Of Protection	IP65

Complementary

Language	Spanish		
	Romanian		
	Turkish		
	Polish		
	Swedish Estonian Bulgarian		
			English
			Russian
	Greek		
	Danish		
	Hungarian		
	Chinese		
	Norwegian		
	Lituanien		
	French		
	Brazilian		
	German		
	Korean Portuguese Finnish Czech		
			Slovak
		Taiwanese	
	Dutch		
	Italian		
	Ukrainian		
Realtime Clock	Built-in		
Battery Size	CR2032		
Battery Life	10 year(s)		
Display Type	Backlit LCD screen white and red		
Messages Display Capacity	8 lines		

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Pixel Resolution	240 x 160
Net Weight	0.44 lb(US) (0.2 kg)

Environment

Ambient Air Temperature For Operation

5...122 °F (-15...50 °C)

Ordering and shipping details

Category	US1CP4E22205
Discount Schedule	CP4E
Gtin	3606480702235
Returnability	Yes
Country Of Origin	ID

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.24 in (5.7 cm)
Package 1 Width	5.39 in (13.7 cm)
Package 1 Length	7.32 in (18.6 cm)
Package 1 Weight	9.31 oz (264.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	20
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	13.38 lb(US) (6.069 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	80
Package 3 Height	17.72 in (45.0 cm)
Package 3 Width	23.62 in (60.0 cm)
Package 3 Length	31.50 in (80.0 cm)
Package 3 Weight	72.26 lb(US) (32.776 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >


Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Circularity Profile	End of Life Information
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration