

Product data sheet

Specifications



kit for UL type 1 conformity, Altivar,
for variable speed drive without
braking unit

VW3A9213

Product availability: Stock - Normally stocked in distribution
facility

Price*: 1,673.33 USD

Main

Accessory / Separate Part Category	Mounting and fixing accessories
Accessory / Separate Part Type	Conformity kit
Degree Of Protection	UL type 1
Product Compatibility	ATV61HC25N4 ATV61HC25N4D ATV61HC25Y ATV61HC31N4 ATV61HC31N4D ATV61HC31Y ATV61HC40Y ATV71HC20N4 ATV71HC20N4D ATV71HC20Y ATV71HC25N4 ATV71HC25N4D ATV71HC25Y ATV71HC28N4 ATV71HC28N4D ATV71HC31Y Variable speed drive ATV630 wall mount 250 kW, normal duty 380...480 V Variable speed drive ATV630 wall mount 315 kW, normal duty 380...480 V Variable speed drive ATV630 wall mount 220 kW, heavy duty 380...480 V Variable speed drive ATV630 wall mount 250 kW, heavy duty 380...480 V Variable speed drive ATV930 wall mount 250 kW, normal duty 380...480 V Variable speed drive ATV930 wall mount 315 kW, normal duty 380...480 V Variable speed drive ATV930 wall mount 250 kW, heavy duty 380...480 V Variable speed drive ATV930 wall mount 200 kW, heavy duty 380...480 V
Accessory / Separate Part Destination	Variable speed drive without braking unit
Range Compatibility	Altivar Process ATV900 Altivar 71 Altivar Process ATV600 Altivar 61

Complementary

Kit Composition	1 EMC plate 1 IP54 casing Fixing accessories 1 UL type 1 cover 1 manual 1 pre-drilled plate for connecting the tubes
Net Weight	42.99 lb(US) (19.5 kg)

Environment

Standards	UL Type 1
-----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	US1CP4C22135
Discount Schedule	CP4C
Gtin	3389119201957
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.45 in (24 cm)
Package 1 Width	19.29 in (49 cm)
Package 1 Length	17.72 in (45 cm)
Package 1 Weight	45.19 lb(US) (20.5 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Reach Free Of Svhc

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov