



power cordset 4x1,5mm² + 2x1mm² + 2x0,14mm² 3 m one end w M23 industrial con.

VW3M5501R30

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 192.55 USD

Main

Range Of Product	Altivar
Accessory / Separate Part Type	Power cable
Accessory / Separate Part Category	Connection accessories
Accessory / Separate Part Destination	Between synchronous motor and variable speed drive
Range Compatibility	Altivar Machine ATV320 Altivar 32
Cable Length	9.84 ft (3 m)
Type Of Cable	Shielded cable

Complementary

Product Compatibility	Synchronous motor BMP 5.51 in (140 mm), 1 C	
•	Synchronous motor BMP 5.51 in (140 mm), 1 F	
	Synchronous motor BMP 5.51 in (140 mm), 2 C	
	Synchronous motor BMP 2.76 in (70 mm), 1 R	
	Synchronous motor BMP 2.76 in (70 mm), 1 F	
	Synchronous motor BMP 2.76 in (70 mm), 2 R	
	Synchronous motor BMP 2.76 in (70 mm), 2 F	
	Synchronous motor BMP 3.94 in (100 mm), 1 R	
	Synchronous motor BMP 3.94 in (100 mm), 1 F	
	Synchronous motor BMP 3.94 in (100 mm), 2 R	
	Synchronous motor BMP 3.94 in (100 mm), 2 F	
Electrical Connection	1 connector M23 8 synchronous motor side	
	1 free end variable speed drive side	
Cable Composition	4 x 1.5 mm² + 2 x 1 mm² + 2 x 0.14 mm²	
Net Weight	1.76 lb(US) (0.8 kg)	

Ordering and shipping details

Category	US1PC5118263
Discount Schedule	PC51
Gtin	3606480564512
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	2.09 in (5.3 cm)
Package 1 Width	8.70 in (22.1 cm)
Package 1 Length	8.70 in (22.1 cm)
Package 1 Weight	32.31 oz (916.0 g)
Unit Type Of Package 2	S04
Number Of Units In Package 2	10
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	15.75 in (40.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Package 2 Weight	21.83 lb(US) (9.904 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov