

Product data sheet

Specifications



power cable 3m shielded 4x
3,3mm², BCH2 brake MIL connector

VW3M5D4FR30

Product availability: Non-Stock - Not normally stocked in
distribution facility

Price*: 630.00 USD

Main

| | |
|---------------------------------------|---|
| Range Of Product | Lexium 28 |
| Product Or Component Type | Power cable |
| Accessory / Separate Part Type | Preassembled power cordset |
| Accessory / Separate Part Category | Connection accessory |
| Product Compatibility | Servo motor BCH2 2000 W 7.09 in (180 mm)) with brake) |
| Accessory / Separate Part Destination | Between servo motor and servo drive |
| Range Compatibility | Lexium 28 |
| Cable Length | 9.84 ft (3 m) |

Complementary

| | |
|-----------------------|---|
| Electrical Connection | Free end servo drive side Connector - MIL big servo motor side |
| Awg Gauge | 6 x AWG 12 |
| Net Weight | 2.09 lb(US) (0.95 kg) |

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US1PC5118263 |
| Discount Schedule | PC51 |
| Gtin | 3606480735790 |
| Returnability | No |
| Country Of Origin | TN |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.38 in (3.5 cm) |
| Package 1 Width | 12.76 in (32.4 cm) |
| Package 1 Length | 14.96 in (38.0 cm) |
| Package 1 Weight | 2.90 lb(US) (1.315 kg) |
| Unit Type Of Package 2 | S02 |
| Number Of Units In Package 2 | 3 |
| Package 2 Height | 5.91 in (15.0 cm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|------------------------|
| Package 2 Width | 11.81 in (30.0 cm) |
| Package 2 Length | 15.75 in (40.0 cm) |
| Package 2 Weight | 9.50 lb(US) (4.307 kg) |

Sustainability






Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

| | | |
|--|---|-----|
|  | Reach Free Of Svhc | |
|  | Toxic Heavy Metal Free | |
|  | Mercury Free | |
|  | Rohs Exemption Information | Yes |
|  | Pvc Free | |
| | | |
| Reach Regulation | REACH Declaration | |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration | |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) | |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov | |